



# MSR Gold™ MiniFastFit (Touring/Stage)

## MSR Gold™ 575/2 MiniFastFit 1CT/4

Thanks to the specially designed lamp base, the MSR Gold™ MiniFastFit takes just seconds to replace, to help ensure non-stop clubbing entertainment. In addition, the innovative gold plated pins ensure excellent current transfer to prolong lamp and lamp holder lifetimes and thereby reduce lamp replacement costs. Easy handling and small compact fixture designs are allowed by the lamps compact size, while the very short arc provides a high perceived brightness and high beam intensity.

#### **Product data**

General Information					
Cap-Base	PGJX28 [ PGJX28]				
Operating Position	UNIVERSAL [ Any or Universal (U)]				
Main Application	Entertainment				
Life To 50% Failures (Nom)	750 h				
System Description	MiniFastFit				
Light Technical					
Color Code	2				
Luminous Flux (Min)	34500 lm				
Luminous Flux (Nom)	38600 lm				
Chromaticity Coordinate X (Nom)	296				
Chromaticity Coordinate Y (Nom)	315				
Correlated Color Temperature (Nom)	7500 K				
Luminous Efficacy (rated) (Nom)	63 lm/W				
Color Rendering Index (Nom)	70				

Operating and Electrical	
Power (Rated) (Nom)	575 W
Lamp Current (Nom)	10.2 A
Ignition Supply Voltage (Min)	198 V
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Cap-Base Information	PGJX28
Luminaire Design Requirements	
Bulb Temperature (Max)	950 °C
Pinch Temperature (Max)	400 °C
Pinch Temperature (Min)	300 °C

Datasheet, 2017, January 30 data subject to change

## MSR Gold™ MiniFastFit (Touring/Stage)


Product Data	
Full product code	871829122109800
Order product name	MSR Gold™ 575/2 MiniFastFit 1CT/4
EAN/UPC - Product	8718291221098
Order code	928184005115
Numerator - Quantity Per Pack	1

Numerator - Packs per outer box	4				
Material Nr. (12NC)	928184005115				
Net Weight (Piece)	0.070 kg				

### Warnings and Safety

• A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


### **Dimensional drawing**




MSR GOLD 575/2 MiniFastFit

Product	D	0	L	L	L	С	F	F	F
MSR Gold™	23.2	3.5	55	57	56	112	36.5	36	35.3
575/2 MiniFastFit	mm	mm	mm	mm	mm	mm	mm	mm	mm
1CT/4									

#### Photometric data





# MSR Gold™ MiniFastFit (Touring/Stage)

